


Varistar CP 19" Panel/Slide Mount, RAL 9005, 42 U, 2000H

Data Solutions

CATALOG NUMBER

24630-013



Slide mount with adjustable increments. Assembly in 600 mm wide cabinets directly on the frame. At 800 mm width adapter bracket for reduced width is necessary, for partial-height mounting depth members are necessary.

FEATURES

19" panel/slide mount with U indicator

Depth-adjustable in 25 mm increments

In accordance with IEC 60297-1 (DIN 41 494, Part 1)

PRODUCT ATTRIBUTES

Rack Height: 42U

Height: 2000mm

Package Quantity: 4

Color: Jet Black

Color Code: RAL 9005

Finish: Powder Coated

Material: Steel

Product Family: Varistar CP

Product Type: Slide Mount

Net Weight: 17.58kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE