

# Special Track Work Mold Only, Signal



## FEATURES

Molds designed for conductor connections to frog and special track work applications

For use on non-load-bearing rail

## SPECIFICATIONS

**Material:** Graphite

Table 1/1

| Catalog Number | Bond Terminal Style | Rail Type      | Conductor Size   | Conductor Outer Diameter, Nominal | Welder Style |
|----------------|---------------------|----------------|------------------|-----------------------------------|--------------|
| SBB343D        | 1 1/2" Tab          | Rail Frog      | 3/16" Bondstrand | 4.76mm                            | TB4          |
| SBB343A        | 3/4" XS             | Manganese Frog | 3/16" Bondstrand | 4.76mm                            | TB4          |
| SBB343C        | 1" Tab              | Manganese Frog | 3/16" Bondstrand | 4.76mm                            | TB4          |
| SBB343E        | 1" Tab              | Manganese Frog | 3/16" Bondstrand | 4.76mm                            | TB4          |
| SBB343B        | 3/4" Tab            | Rail Frog      | 3/16" Bondstrand | 4.76mm                            | TB4          |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE