

Transposition Sections 90-Degree Elbow CCW, 4.00x4.00, Gray, Steel

CATALOG NUMBER

F44LE9KOKT



Lay-in Hinged-Cover Transposition Sections are used when it is necessary to rotate the open side of the wireway run by 90 degrees and still retain the lay-in feature.

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

FEATURES

Lay-in Hinged-Cover Transposition Sections are used when it is necessary to rotate the open side of the wireway run by 90 degrees and still retain the lay-in feature

PRODUCT ATTRIBUTES

Type: Transposition Section

Height (H): 102mm

Width (W): 102mm

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness (T): 1.9mm


Sealing Plate Quantity: 1

Sealing Plate Type: Flat

ADDITIONAL PRODUCT DETAILS

Each sealing plate also includes one gasket and one set of screws to join sections.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE