

19" Fan Unit, 1 U, Speed Control and Monitoring

Power Utilities

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICATIONS



FEATURES

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage AC	Input Voltage DC	Certifications
10713-098		24 V min	RoHS, CE, EAC
10713-099		24 V min	RoHS, CE, EAC

Catalog Number	Input Voltage AC	Input Voltage DC	Certifications
19713-006	230 V min		RoHS, EAC
19713-121	230 V min		RoHS, EAC

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE