

# Varistar CP Base/Plinth

## Power Utilities

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

### FEATURES

2 support profiles, for front and rear

Static load-carrying capacity 1000 kg

### SPECIFICATIONS

Table 1/2

Catalog Number	Height	Width	Color	Color Code	Depth	Finish
24630-035	100 mm	800 mm	Black Grey	RAL 7021		Powder Coated
24630-065	100 mm	800 mm	Black Grey	RAL 7021		Powder Coated
24630-034	100 mm	600 mm	Black Grey	RAL 7021	600 mm	Powder Coated
24630-064	100 mm	600 mm	Black Grey	RAL 7021		Powder Coated
24630-067	200 mm	800 mm	Black Grey	RAL 7021		Powder Coated
24630-036	200 mm	600 mm	Black Grey	RAL 7021		Powder Coated
24630-066	200 mm	600 mm	Black Grey	RAL 7021		Powder Coated
24630-037	200 mm	800 mm	Black Grey	RAL 7021		Powder Coated

Table 2/2

Catalog Number	Material	Product Type	Type
----------------	----------	--------------	------

24630-035	Steel	Cabinet/Rack Base	Base Plinth
24630-065	Steel	Cabinet/Rack Base	Base Plinth
24630-034	Steel	Cabinet/Rack Base	Base Plinth
24630-064	Steel	Cabinet/Rack Base	Base Plinth
24630-067	Steel	Cabinet/Rack Base	Base Plinth
24630-036	Steel	Cabinet/Rack Base	Base Plinth
24630-066	Steel	Cabinet/Rack Base	Base Plinth
24630-037	Steel	Cabinet/Rack Base	Base Plinth

## ADDITIONAL PRODUCT DETAILS

---

Please order side trims separately.

Cannot be used in conjunction with castors

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**