

# Varistar CP Frame

## Power Utilities

Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration.

### FEATURES

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

### SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Height	Width	Depth	Color	Color Code
20630-065	24 U	1200 mm	600 mm	600 mm	Black Grey	RAL 7021
20630-066	24 U	1200 mm	600 mm	800 mm	Black Grey	RAL 7021
20630-067	24 U	1200 mm	600 mm	900 mm	Black Grey	RAL 7021
20630-068	24 U	1200 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-071	24 U	1200 mm	800 mm	600 mm	Black Grey	RAL 7021
20630-072	24 U	1200 mm	800 mm	800 mm	Black Grey	RAL 7021
20630-073	24 U	1200 mm	800 mm	900 mm	Black Grey	RAL 7021
20630-074	24 U	1200 mm	800 mm	1000 mm	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Depth	Color	Color Code
20630-075	29 U	1400 mm	600 mm	600 mm	Black Grey	RAL 7021
20630-076	29 U	1400 mm	600 mm	800 mm	Black Grey	RAL 7021
20630-077	29 U	1400 mm	600 mm	900 mm	Black Grey	RAL 7021
20630-078	29 U	1400 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-079	29 U	1400 mm	800 mm	600 mm	Black Grey	RAL 7021
20630-080	29 U	1400 mm	800 mm	800 mm	Black Grey	RAL 7021
20630-081	29 U	1400 mm	800 mm	900 mm	Black Grey	RAL 7021
20630-082	29 U	1400 mm	800 mm	1000 mm	Black Grey	RAL 7021
20630-083	33 U	1600 mm	600 mm	600 mm	Black Grey	RAL 7021
20630-084	33 U	1600 mm	600 mm	800 mm	Black Grey	RAL 7021
20630-085	33 U	1600 mm	600 mm	900 mm	Black Grey	RAL 7021
20630-086	33 U	1600 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-087	33 U	1600 mm	800 mm	600 mm	Black Grey	RAL 7021
20630-088	33 U	1600 mm	800 mm	800 mm	Black Grey	RAL 7021
20630-089	33 U	1600 mm	800 mm	900 mm	Black Grey	RAL 7021
20630-090	33 U	1600 mm	800 mm	1000 mm	Black Grey	RAL 7021
20630-091	38 U	1800 mm	600 mm	600 mm	Black Grey	RAL 7021
20630-092	38 U	1800 mm	600 mm	800 mm	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Depth	Color	Color Code
20630-093	38 U	1800 mm	600 mm	900 mm	Black Grey	RAL 7021
20630-094	38 U	1800 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-095	38 U	1800 mm	800 mm	600 mm	Black Grey	RAL 7021
20630-096	38 U	1800 mm	800 mm	800 mm	Black Grey	RAL 7021
20630-097	38 U	1800 mm	800 mm	900 mm	Black Grey	RAL 7021
20630-098	38 U	1800 mm	800 mm	1000 mm	Black Grey	RAL 7021
20630-099	42 U	2000 mm	600 mm	600 mm	Black Grey	RAL 7021
20630-100	42 U	2000 mm	600 mm	800 mm	Black Grey	RAL 7021
20630-101	42 U	2000 mm	600 mm	900 mm	Black Grey	RAL 7021
20630-102	42 U	2000 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-103	42 U	2000 mm	600 mm	1100 mm	Black Grey	RAL 7021
20630-104	42 U	2000 mm	600 mm	1200 mm	Black Grey	RAL 7021
20630-105	42 U	2000 mm	800 mm	600 mm	Black Grey	RAL 7021
20630-106	42 U	2000 mm	800 mm	800 mm	Black Grey	RAL 7021
20630-107	42 U	2000 mm	800 mm	900 mm	Black Grey	RAL 7021
20630-108	42 U	2000 mm	800 mm	1000 mm	Black Grey	RAL 7021
20630-109	42 U	2000 mm	800 mm	1100 mm	Black Grey	RAL 7021
20630-110	42 U	2000 mm	800 mm	1200 mm	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Depth	Color	Color Code
20630-261	42 U	2000 mm	600 mm	300 mm	Black Grey	RAL 7021
20630-111	47 U	2200 mm	600 mm	600 mm	Black Grey	RAL 7021
20630-112	47 U	2200 mm	600 mm	800 mm	Black Grey	RAL 7021
20630-113	47 U	2200 mm	600 mm	900 mm	Black Grey	RAL 7021
20630-114	47 U	2200 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-115	47 U	2200 mm	600 mm	1100 mm	Black Grey	RAL 7021
20630-116	47 U	2200 mm	600 mm	1200 mm	Black Grey	RAL 7021
20630-117	47 U	2200 mm	800 mm	600 mm	Black Grey	RAL 7021
20630-118	47 U	2200 mm	800 mm	800 mm	Black Grey	RAL 7021
20630-119	47 U	2200 mm	800 mm	900 mm	Black Grey	RAL 7021
20630-120	47 U	2200 mm	800 mm	1000 mm	Black Grey	RAL 7021
20630-121	47 U	2200 mm	800 mm	1100 mm	Black Grey	RAL 7021
20630-122	47 U	2200 mm	800 mm	1200 mm	Black Grey	RAL 7021
20630-262	47 U	2200 mm	600 mm	300 mm	Black Grey	RAL 7021
20630-123	52 U	2450 mm	600 mm	1000 mm	Black Grey	RAL 7021
20630-124	52 U	2450 mm	600 mm	1100 mm	Black Grey	RAL 7021
20630-125	52 U	2450 mm	600 mm	1200 mm	Black Grey	RAL 7021
20630-126	52 U	2450 mm	800 mm	1000 mm	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Depth	Color	Color Code
20630-127	52 U	2450 mm	800 mm	1100 mm	Black Grey	RAL 7021
20630-128	52 U	2450 mm	800 mm	1200 mm	Black Grey	RAL 7021

Table 2/3

Catalog Number	Complies With	Frame Material	Material	Product Type	Static Load	Type
20630-065		Steel	Steel	Cabinet/Rack Frame		Standard
20630-066		Steel	Steel	Cabinet/Rack Frame		Standard
20630-067		Steel	Steel	Cabinet/Rack Frame		Standard
20630-068		Steel	Steel	Cabinet/Rack Frame		Standard
20630-071		Steel	Steel	Cabinet/Rack Frame		Standard
20630-072		Steel	Steel	Cabinet/Rack Frame		Standard
20630-073		Steel	Steel	Cabinet/Rack Frame		Standard
20630-074		Steel	Steel	Cabinet/Rack Frame		Standard
20630-075		Steel	Steel	Cabinet/Rack Frame		Standard
20630-076		Steel	Steel	Cabinet/Rack Frame		Standard
20630-077		Steel	Steel	Cabinet/Rack Frame		Standard
20630-078		Steel	Steel	Cabinet/Rack Frame		Standard
20630-079		Steel	Steel	Cabinet/Rack Frame		Standard
20630-080		Steel	Steel	Cabinet/Rack Frame		Standard
20630-081		Steel	Steel	Cabinet/Rack Frame		Standard

CatalogNumber	Complies With	Frame Material	Material	Product Type	Static Load	Type
20630-082		Steel	Steel	Cabinet/Rack Frame		Standard
20630-083		Steel	Steel	Cabinet/Rack Frame		Standard
20630-084		Steel	Steel	Cabinet/Rack Frame		Standard
20630-085		Steel	Steel	Cabinet/Rack Frame		Standard
20630-086		Steel	Steel	Cabinet/Rack Frame		Standard
20630-087		Steel	Steel	Cabinet/Rack Frame		Standard
20630-088		Steel	Steel	Cabinet/Rack Frame		Standard
20630-089		Steel	Steel	Cabinet/Rack Frame		Standard
20630-090		Steel	Steel	Cabinet/Rack Frame		Standard
20630-091		Steel	Steel	Cabinet/Rack Frame		Standard
20630-092		Steel	Steel	Cabinet/Rack Frame		Standard
20630-093		Steel	Steel	Cabinet/Rack Frame		Standard
20630-094		Steel	Steel	Cabinet/Rack Frame		Standard
20630-095		Steel	Steel	Cabinet/Rack Frame		Standard
20630-096		Steel	Steel	Cabinet/Rack Frame		Standard
20630-097		Steel	Steel	Cabinet/Rack Frame		Standard
20630-098		Steel	Steel	Cabinet/Rack Frame		Standard
20630-099		Steel	Steel	Cabinet/Rack Frame		Standard

CatalogNumber	Complies With	Frame Material	Material	Product Type	Static Load	Type
20630-100		Steel	Steel	Cabinet/Rack Frame		Standard
20630-101		Steel	Steel	Cabinet/Rack Frame		Standard
20630-102	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-103	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-104	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-105		Steel	Steel	Cabinet/Rack Frame		Standard
20630-106		Steel	Steel	Cabinet/Rack Frame		Standard
20630-107		Steel	Steel	Cabinet/Rack Frame		Standard
20630-108	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-109	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-110	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-261		Steel	Steel	Cabinet/Rack Frame		Standard
20630-111		Steel	Steel	Cabinet/Rack Frame		Standard
20630-112		Steel	Steel	Cabinet/Rack Frame		Standard
20630-113		Steel	Steel	Cabinet/Rack Frame		Standard
20630-114	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-115	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-116	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard

CatalogNumber	Complies With	Frame Material	Material	Product Type	Static Load	Type
20630-117		Steel	Steel	Cabinet/Rack Frame		Standard
20630-118		Steel	Steel	Cabinet/Rack Frame		Standard
20630-119		Steel	Steel	Cabinet/Rack Frame		Standard
20630-120	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-121	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-122	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-262		Steel	Steel	Cabinet/Rack Frame		Standard
20630-123	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-124	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-125	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-126	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-127	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard
20630-128	IEC 61587-1, IEC 61587-3	Steel	Steel	Cabinet/Rack Frame	1600 kgf	Standard

Table 3/3

Catalog Number	Works With
20630-065	Varistar CP
20630-066	Varistar CP
20630-067	Varistar CP
20630-068	Varistar CP



Catalog Number	Works With
20630-071	Varistar CP
20630-072	Varistar CP
20630-073	Varistar CP
20630-074	Varistar CP
20630-075	Varistar CP
20630-076	Varistar CP
20630-077	Varistar CP
20630-078	Varistar CP
20630-079	Varistar CP
20630-080	Varistar CP
20630-081	Varistar CP
20630-082	Varistar CP
20630-083	Varistar CP
20630-084	Varistar CP
20630-085	Varistar CP
20630-086	Varistar CP
20630-087	Varistar CP
20630-088	Varistar CP

Catalog Number	Works With
20630-089	Varistar CP
20630-090	Varistar CP
20630-091	Varistar CP
20630-092	Varistar CP
20630-093	Varistar CP
20630-094	Varistar CP
20630-095	Varistar CP
20630-096	Varistar CP
20630-097	Varistar CP
20630-098	Varistar CP
20630-099	Varistar CP
20630-100	Varistar CP
20630-101	Varistar CP
20630-102	Varistar CP
20630-103	Varistar CP
20630-104	Varistar CP
20630-105	Varistar CP
20630-106	Varistar CP

Catalog Number	Works With
20630-107	Varistar CP
20630-108	Varistar CP
20630-109	Varistar CP
20630-110	Varistar CP
20630-261	Varistar CP
20630-111	Varistar CP
20630-112	Varistar CP
20630-113	Varistar CP
20630-114	Varistar CP
20630-115	Varistar CP
20630-116	Varistar CP
20630-117	Varistar CP
20630-118	Varistar CP
20630-119	Varistar CP
20630-120	Varistar CP
20630-121	Varistar CP
20630-122	Varistar CP
20630-262	Varistar CP

Catalog Number	Works With
20630-123	Varistar CP
20630-124	Varistar CP
20630-125	Varistar CP
20630-126	Varistar CP
20630-127	Varistar CP
20630-128	Varistar CP

## ADDITIONAL PRODUCT DETAILS

---

A combination of castors and castors with adjustable feet is not possible with the standard frame. Please order the mobile frame for this requirement

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**