

# Varistar CP Steel Door, Perforated With 3-Point Electronic Locking

## Power Utilities

Varistar CP perforated steel door 3-point locking for IP 20 applications.

### FEATURES

Perforated steel door with 3-point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

### SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Height  | Width  | Type                   | Color      | Color Code |
|----------------|-------------|---------|--------|------------------------|------------|------------|
| 21630-814      | 42 U        | 2000 mm | 600 mm | Steel Door, Perforated | Black Grey | RAL 7021   |
| 21630-815      | 47 U        | 2200 mm | 600 mm | Steel Door, Perforated | Black Grey | RAL 7021   |
| 21630-816      | 52 U        | 2450 mm | 600 mm | Steel Door, Perforated | Black Grey | RAL 7021   |
| 21630-817      | 42 U        | 2000 mm | 800 mm | Steel Door, Perforated | Black Grey | RAL 7021   |
| 21630-818      | 47 U        | 2200 mm | 800 mm | Steel Door, Perforated | Black Grey | RAL 7021   |
| 21630-819      | 52 U        | 2450 mm | 800 mm | Steel Door, Perforated | Black Grey | RAL 7021   |
| 21630-895      | 42 U        | 2000 mm | 600 mm | Steel Door, Perforated | Black Grey | RAL 7021   |
| 21630-896      | 47 U        | 2200 mm | 600 mm | Steel Door, Perforated | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height  | Width  | Type                      | Color      | Color Code |
|---------------|-------------|---------|--------|---------------------------|------------|------------|
| 21630-897     | 52 U        | 2450 mm | 600 mm | Steel Door,<br>Perforated | Black Grey | RAL 7021   |
| 21630-898     | 42 U        | 2000 mm | 800 mm | Steel Door,<br>Perforated | Black Grey | RAL 7021   |
| 21630-899     | 42 U        | 2000 mm | 800 mm | Steel Door,<br>Perforated | Black Grey | RAL 7021   |
| 21630-900     | 52 U        | 2450 mm | 800 mm | Steel Door,<br>Perforated | Black Grey | RAL 7021   |

| Table 2/3      |               |               |                                |          |              |                   |
|----------------|---------------|---------------|--------------------------------|----------|--------------|-------------------|
| Catalog Number | Complies With | Finish        | Locking Type                   | Material | Product Type | Protection Rating |
| 21630-814      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-815      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-816      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-817      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-818      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-819      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-895      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-896      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-897      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-898      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-899      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |
| 21630-900      | IEC 61587-1   | Powder Coated | 3-Point Locking,<br>Electronic | Steel    | Cabinet Door | IP20              |

Table 3/3

| Catalog Number | Works With  |
|----------------|-------------|
| 21630-814      | Varistar CP |
| 21630-815      | Varistar CP |
| 21630-816      | Varistar CP |
| 21630-817      | Varistar CP |
| 21630-818      | Varistar CP |
| 21630-819      | Varistar CP |
| 21630-895      | Varistar CP |
| 21630-896      | Varistar CP |
| 21630-897      | Varistar CP |
| 21630-898      | Varistar CP |
| 21630-899      | Varistar CP |
| 21630-900      | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**