

# Cable to Web of Rail Mold Only, Signal



## FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

## SPECIFICATIONS

**Rail Type:** 85 lb to 141 lb T-Rail Sections

**Material:** Graphite

Table 1/1

Catalog Number	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
SBW3150BRH	1" Tab	3/16" Bondstrand	4.76mm	TB5	Right Hand
SBB200CRH	1" Tab	3/16" Bondstrand	4.76mm	TB5, T21	Right Hand
SBB200CLH	1" Tab	3/16" Bondstrand	4.76mm	TB5, T21	Left Hand
SBW3150BLH	1" Tab	3/16" Bondstrand	4.76mm	TB5	Left Hand
SBB200YLH	1" Tab	16 mm <sup>2</sup> Concentric	5.18mm	T21, TB5	Left Hand
SBB200YRH	1" Tab	16 mm <sup>2</sup> Concentric	5.18mm	T21, TB5	Right Hand

Catalog Number	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
SBB200XRH	1" Tab	25 mm <sup>2</sup> Stranded	6.6mm	TB5, T21	Right Hand
SBB200PRH	1" Tab	35 mm <sup>2</sup> Stranded	7.75mm	TB5, T21	Right Hand
SBB200PLH	1" Tab	35 mm <sup>2</sup> Stranded	7.75mm	TB5, T21	Left Hand
SBWW6RH	Field-made	50 mm <sup>2</sup> Solid	8mm	T21	Right Hand
SBWW6LH	Field-made	50 mm <sup>2</sup> Solid	8mm	T21	Left Hand

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE