


# RatiopacPRO 19" Mounting Bracket With Handle, Retrofitting



With this 19" mounting bracket with handles the flexible and robust RatiopacPRO/-AIR case, is simple to convert from desktop to 19" rack-mountable.

## CERTIFICATIONS



## FEATURES

For conversion of cases with cover strip, front handle or 19" mounting bracket

## SPECIFICATIONS

**Material:** Aluminum  
**Product Type:** Handle  
**Type:** Static

Table 1/2

Catalog Number	Package Quantity	Handle Type	Color	Finish	Product Family	Works With
24572-700	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO

CatalogNumber	Package Quantity	Handle Type	Color	Finish	Product Family	Works With
24572-701	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO
24572-702	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO
24572-704	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO
24572-705	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO AIR	Cases, RatiopacPRO AIR
24572-707	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO AIR	Cases, RatiopacPRO AIR

Table 2/2

Catalog Number	Quick Ship
24572-700	No
24572-701	No
24572-702	No
24572-704	No
24572-705	No
24572-707	No

## ADDITIONAL PRODUCT DETAILS

No slide rails may be used when fitting into cabinets or 19" cases.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**