

Telescopic Slide Universal, Slim, 2 U

Slim Universal Telescopic Slide, 2 U.



CERTIFICATIONS



FEATURES

Rail width k = 9.7 mm, max. installation width of extension/drawer w = 429 mm

Lateral mounting on the 19" uprights (19" plane remains free for fixing the extension/drawer)

Locking at full extension

Static load-carrying capacity per pair 46 - 57 kg

Extension length > 110 %

SPECIFICATIONS

| | |
|----------------------|------------------|
| Material: | Steel |
| Product Type: | Telescopic Slide |
| Finish: | Zinc Plated |

Table 1/1

| Catalog Number | Length | Package Quantity | Static Load | Type | Quick Ship |
|----------------|--------|------------------|-------------|-----------|------------|
| 20110-071 | 356mm | 2 | 57kg | Universal | No |

| Catalog Number | Length | Package Quantity | Static Load | Type | Quick Ship |
|----------------|--------|------------------|-------------|-----------|------------|
| 20110-072 | 406mm | 2 | 55kg | Universal | No |
| 20110-073 | 457mm | 2 | 55kg | Universal | No |
| 20110-074 | 508mm | 2 | 55kg | Universal | No |
| 20110-075 | 559mm | 2 | 46kg | Universal | No |
| 20110-076 | 584mm | 2 | 46kg | Universal | No |
| 20110-077 | 610mm | 2 | 46kg | Universal | No |

ADDITIONAL PRODUCT DETAILS

Universal telescopic Rails can also be fitted without additional components in non-standard applications, this also in other than 19" cabinets.

To mount on 19" plane please order assembly kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE