

# Varistar CP Mobile Frame

## Data Solutions



Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration. For mobile applications.

### FEATURES

Welded, finish powder-coated, black gray, RAL 7021

### SPECIFICATIONS

|                      |                    |
|----------------------|--------------------|
| <b>Dynamic Load:</b> | 1000kg             |
| <b>Static Load:</b>  | 1600kg             |
| <b>Product Type:</b> | Cabinet/Rack Frame |
| <b>Material:</b>     | Steel              |

Table 1/2

| Catalog Number | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-247      | 47U         | 2200mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-248      | 47U         | 2200mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-249      | 47U         | 2200mm | 800mm | 1100mm | 1                | Black Grey |
| 20630-250      | 47U         | 2200mm | 800mm | 1200mm | 1                | Black Grey |
| 20630-251      | 52U         | 2450mm | 600mm | 1000mm | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|---------------|-------------|--------|-------|--------|------------------|------------|
| 20630-252     | 52U         | 2450mm | 600mm | 1100mm | 1                | Black Grey |
| 20630-253     | 52U         | 2450mm | 600mm | 1200mm | 1                | Black Grey |
| 20630-254     | 52U         | 2450mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-255     | 52U         | 2450mm | 800mm | 1100mm | 1                | Black Grey |
| 20630-256     | 52U         | 2450mm | 800mm | 1200mm | 1                | Black Grey |
| 20630-193     | 24U         | 1200mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-194     | 24U         | 1200mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-195     | 24U         | 1200mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-196     | 24U         | 1200mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-199     | 24U         | 1200mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-200     | 24U         | 1200mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-201     | 24U         | 1200mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-202     | 24U         | 1200mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-203     | 29U         | 1400mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-204     | 29U         | 1400mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-205     | 29U         | 1400mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-206     | 29U         | 1400mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-207     | 29U         | 1400mm | 800mm | 600mm  | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|---------------|-------------|--------|-------|--------|------------------|------------|
| 20630-208     | 29U         | 1400mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-209     | 29U         | 1400mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-210     | 29U         | 1400mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-211     | 33U         | 1600mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-212     | 33U         | 1600mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-213     | 33U         | 1600mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-214     | 33U         | 1600mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-215     | 33U         | 1600mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-216     | 33U         | 1600mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-217     | 33U         | 1600mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-218     | 33U         | 1600mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-219     | 38U         | 1800mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-220     | 38U         | 1800mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-221     | 38U         | 1800mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-222     | 38U         | 1800mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-223     | 38U         | 1800mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-224     | 38U         | 1800mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-225     | 38U         | 1800mm | 800mm | 900mm  | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|---------------|-------------|--------|-------|--------|------------------|------------|
| 20630-226     | 38U         | 1800mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-227     | 42U         | 2000mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-228     | 42U         | 2000mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-229     | 42U         | 2000mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-230     | 42U         | 2000mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-231     | 42U         | 2000mm | 600mm | 1100mm | 1                | Black Grey |
| 20630-232     | 42U         | 2000mm | 600mm | 1200mm | 1                | Black Grey |
| 20630-233     | 42U         | 2000mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-234     | 42U         | 2000mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-235     | 42U         | 2000mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-236     | 42U         | 2000mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-237     | 42U         | 2000mm | 800mm | 1100mm | 1                | Black Grey |
| 20630-238     | 42U         | 2000mm | 800mm | 1200mm | 1                | Black Grey |
| 20630-239     | 47U         | 2200mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-240     | 47U         | 2200mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-241     | 47U         | 2200mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-242     | 47U         | 2200mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-243     | 47U         | 2200mm | 600mm | 1100mm | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|---------------|-------------|--------|-------|--------|------------------|------------|
| 20630-244     | 47U         | 2200mm | 600mm | 1200mm | 1                | Black Grey |
| 20630-245     | 47U         | 2200mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-246     | 47U         | 2200mm | 800mm | 800mm  | 1                | Black Grey |

| Table 2/2      |            |                          |                |        |             |
|----------------|------------|--------------------------|----------------|--------|-------------|
| Catalog Number | Color Code | Complies With            | Frame Material | Type   | Works With  |
| 20630-247      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-248      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-249      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-250      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-251      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-252      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-253      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-254      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-255      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-256      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-193      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-194      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-195      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-196      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |

| Catalog Number | Color Code | Complies With            | Frame Material | Type   | Works With  |
|----------------|------------|--------------------------|----------------|--------|-------------|
| 20630-199      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-200      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-201      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-202      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-203      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-204      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-205      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-206      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-207      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-208      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-209      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-210      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-211      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-212      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-213      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-214      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-215      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-216      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |

| Catalog Number | Color Code | Complies With            | Frame Material | Type   | Works With  |
|----------------|------------|--------------------------|----------------|--------|-------------|
| 20630-217      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-218      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-219      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-220      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-221      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-222      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-223      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-224      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-225      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-226      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-227      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-228      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-229      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-230      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-231      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-232      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-233      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-234      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |

| Catalog Number | Color Code | Complies With            | Frame Material | Type   | Works With  |
|----------------|------------|--------------------------|----------------|--------|-------------|
| 20630-235      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-236      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-237      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-238      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-239      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-240      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-241      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-242      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-243      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-244      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-245      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |
| 20630-246      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Mobile | Varistar CP |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.





Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**