

Industrial Stack Lay-in Terminal Holder



CERTIFICATIONS



FEATURES

Air terminal or cable holder for lay-in brick construction

SPECIFICATIONS

Material: Brass

Table 1/2

Catalog Number	Diameter (Ø)	Depth (D)	Height (H)	Width (W)	A	B
LPC49234	18.29 mm	127mm	26.4 mm	72.14 mm	97.6 mm	29 mm
LPC49258	14.96 mm	127mm	26.4 mm	72.14 mm	97.6 mm	29 mm
LPLC49258	14.96 mm	127mm	26.4 mm	72.14 mm	97.6 mm	29 mm
LPLC49234	18.29 mm	127mm	26.4 mm	72.14 mm	97.6 mm	29 mm


Table 2/2

Catalog Number	Unit Weight	Certifications
LPC49234	0.28 kg	
LPC49258	0.28 kg	
LPLC49258	0.82 kg	E202878-Combined_CoC, E202878-Combined_CoC
LPLC49234	0.82 kg	E202878-Combined_CoC, E202878-Combined_CoC

ADDITIONAL PRODUCT DETAILS

Where applicable, lead covering thickness is a minimum of 1/16" (1.59 mm) and is not included in the stated dimensions.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE