nVent | HOFFMAN

We connect and protect

ProLine G2 Vented Plinth Base Cover, 800, Steel, Black

CATALOG NUMBER

P2APBVC8

The Vented Plinth Base Covers replace the traditional solid plinth base covers that mount width-wise across the front and rear of the enclosure. Vented covers allow air to enter the enclosure from below, and are used in conjunction with the Vented Gland Plate.

FEATURES

Mounting hardware included

PRODUCT ATTRIBUTES

Article Number: 36148
Frame Type: Single-Bay
Finish: Powder Coated
Fits Frame Width: 800mm
Color: Jet Black
Color Code: RAL 9005
Material: Mild Steel
Thickness: 1.52mm

ADDITIONAL PRODUCT DETAILS

Please note that a standard 100mm Solid Plinth Base must be ordered separately, as Vented Plinth Base Covers are replacements for the front and rear covers only. Vented Gland Plate also sold separately, but required for successful air passage.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.