

Fusion G7 Horizontal Separator



Horizontal Separator mounts onto side-mount accessory rails to divide the Fusion G7 into separate compartments.

FEATURES

Galvanized 1.5-mm thick(16 gauge) steel.

Mounting hardware provided.

SPECIFICATIONS

Table 1/1					
Catalog Number	Material	Finish	Thickness	Fits Frame	Quick Ship
FUSW3015G010S	Mild Steel	Galvanized	1.5mm	300 x 150mm	No
FUSW3022G010S	Mild Steel	Galvanized	1.5mm	300 x 225mm	No
FUSW4020G010S	Mild Steel	Galvanized	1.5mm	400 x 200mm	No
FUSW4022G010S	Mild Steel	Galvanized	1.5mm	400 x 225mm	No
FUSW5020G010S	Mild Steel	Galvanized	1.5mm	500 x 200mm	No
FUSW5022G010S	Mild Steel	Galvanized	1.5mm	500 x 225mm	No
FUSW5025G010S	Mild Steel	Galvanized	1.5mm	500 x 250mm	No
FUSW5030G010S	Mild Steel	Galvanized	1.5mm	500 x 300mm	No
FUSW6022G010S	Mild Steel	Galvanized	1.5mm	600 x 225mm	No
FUSW6025G010S	Mild Steel	Galvanized	1.5mm	600 x 250mm	No
FUSW6030G010S	Mild Steel	Galvanized	1.5mm	600 x 300mm	No
FUSW6032G010S	Mild Steel	Galvanized	1.5mm	600 x 325mm	No
FUSW6040G010S	Mild Steel	Galvanized	1.5mm	600 x 400mm	No
FUSW8030G010S	Mild Steel	Galvanized	1.5mm	800 x 300mm	No
FUSW8040G010S	Mild Steel	Galvanized	1.5mm	800 x 400mm	No
FUSW9032G010S	Mild Steel	Galvanized	1.5mm	900 x 325mm	No
FUSW9042G010S	Mild Steel	Galvanized	1.5mm	900 x 425mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE