

# 19" Front Panel, Vented

Vented front panels allows heat dissipation through holes.



## CERTIFICATIONS



## FEATURES

Vented front panels (Aluminum ) allows heat dissipation

## SPECIFICATIONS

|                        |             |
|------------------------|-------------|
| <b>Rack Width:</b>     | 95HP        |
| <b>Material:</b>       | Aluminum    |
| <b>Accessory Type:</b> | Front panel |
| <b>Product Type:</b>   | Front Panel |

Table 1/3

| Catalog Number | Rack Height | Finish        | Mounting       | Package Quantity | Front Finish | Rear Finish |
|----------------|-------------|---------------|----------------|------------------|--------------|-------------|
| 30118-962      | 1U          | Powder Coated | Screw-on Front | 1                | Painted      | Painted     |
| 30702-044      | 1U          | Anodized      | Screw-on Front | 1                | Raw          | Conductive  |
| 30702-047      | 1U          | Anodized      | Screw-on Front | 1                | Anodized     | Anodized    |

| CatalogNumber | Rack Height | Finish        | Mounting       | Package Quantity | Front Finish | Rear Finish |
|---------------|-------------|---------------|----------------|------------------|--------------|-------------|
| 30702-056     | 1U          | Powder Coated | Screw-on Front | 1                | Painted      | Painted     |
| 30118-963     | 2U          | Anodized      | Screw-on Front | 1                | Painted      | Painted     |
| 30118-964     | 3U          | Powder Coated | Screw-on Front | 1                | Painted      | Painted     |
| 30702-045     | 2U          | Anodized      | Screw-on Front | 1                | Raw          | Raw         |
| 30702-046     | 3U          | Anodized      | Screw-on Front | 1                | Raw          | Raw         |
| 30702-048     | 2U          | Anodized      | Screw-on Front | 1                | Anodized     | Anodized    |
| 30702-049     | 3U          | Anodized      | Screw-on Front | 1                | Anodized     | Anodized    |
| 30702-057     | 2U          | Powder Coated | Screw-on Front | 1                | Painted      | Painted     |
| 30702-058     | 3U          | Powder Coated | Screw-on Front | 1                | Painted      | Painted     |

Table 2/3

| Catalog Number | Treated Edges | Color Code | EMC Shielding | Height (H) | Type            | Width (W) |
|----------------|---------------|------------|---------------|------------|-----------------|-----------|
| 30118-962      |               | RAL 7021   | No            | 43.6mm     | 19" Front Panel | 483mm     |
| 30702-044      |               |            | No            | 43.6mm     | 19" Front Panel | 483mm     |
| 30702-047      | Yes           |            | No            | 43.6mm     | 19" Front Panel | 483mm     |
| 30702-056      |               | RAL 7035   | No            | 43.6mm     | 19" Front Panel | 483mm     |
| 30118-963      |               | RAL 7021   | No            | 88.1mm     | 19" Front Panel | 483mm     |
| 30118-964      |               | RAL 7021   | No            | 132.5mm    | 19" Front Panel | 483mm     |
| 30702-045      |               |            | No            | 88.1mm     | 19" Front Panel | 483mm     |

| CatalogNumber | Treated Edges | Color Code | EMC Shielding | Height (H) | Type            | Width (W) |
|---------------|---------------|------------|---------------|------------|-----------------|-----------|
| 30702-046     |               |            | No            | 132.5mm    | 19" Front Panel | 483mm     |
| 30702-048     | Yes           |            | No            | 88.1mm     | 19" Front Panel | 483mm     |
| 30702-049     | Yes           |            | No            | 132.5mm    | 19" Front Panel | 483mm     |
| 30702-057     |               | RAL 7035   | No            | 88.1mm     | 19" Front Panel | 483mm     |
| 30702-058     |               | RAL 7035   | No            | 132.5mm    | 19" Front Panel | 483mm     |

Table 3/3

| Catalog Number | Quick Ship |
|----------------|------------|
| 30118-962      | No         |
| 30702-044      | No         |
| 30702-047      | No         |
| 30702-056      | No         |
| 30118-963      | No         |
| 30118-964      | No         |
| 30702-045      | No         |
| 30702-046      | No         |
| 30702-048      | No         |
| 30702-049      | No         |
| 30702-057      | No         |
| 30702-058      | No         |

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE