nVent | SCHROFF

We connect and protect

# Interscale Mounting Bracket for 70 mm Flexible Heat Conductor (FHC), AMD CPU

## CATALOG NUMBER

**24830-003**





The mounting bracket enables a user to assemble an Intel or AMD processor.

## CERTIFICATIONS

RoHS COMPLIANT

## FEATURES

- Designed for ATX/ITX/Mini ITX & COM using Intel core-i processors and AMD processors with the following sockets: Intel: LGA775, LGA1150, LGA1155, LGA1156, LGA1366, LGA2011 ; AMD: AM2, AM2(+), AM3, AM3(+), FM1, FM2, FM2(+)
- Utilizes keep out zones to not interfere with other board components
- Designed to assemble the 70 mm Flexible Heat Conductor to thhe CPU

## PRODUCT ATTRIBUTES

- Design Feature: AMD CPU
- Package Quantity: 1
- Finish: Aluminum-Zinc Plated
- Material: Steel
- Product Family: Interscale

| |
|---|
| Product Type: Bracket |
| Type: CPU Adpater |
| Works With: Cases |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.


**North America**
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

**Europe**
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

**Asia**
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

**Middle East & India**
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff


Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**


©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.