

HD Heavy Duty Pipe Clamp



CERTIFICATIONS



FEATURES

Fillet welded connector nut has flats to accommodate spanners

Easy open flange for pipe sizes less than 4"

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

SPECIFICATIONS

Color:	Black
Finish:	Electrogalvanized
Material:	Steel;EPDM-SBR Rubber
Temperature:	-50 to 110 °C

Table 1/2

Catalog Number	Article Number	Outer Diameter (OD)	NB/DN	Rod Size (RS)	Width (W)	Thickness (T)
HDI018	577033	14 - 18 mm	10	M8, M10	30 mm	2.5 mm

CatalogNumber	Article Number	Outer Diameter (OD)	NB/DN	Rod Size (RS)	Width (W)	Thickness (T)
HDI023	577034	19 - 23 mm	15	M8, M10	30 mm	2.5 mm
HDI028	577035	24 - 28 mm	20	M8, M10	30 mm	2.5 mm
HDI037	577037	33 - 37 mm		M8, M10	30 mm	2.5 mm
HDI045	577038	40 - 45 mm	32	M8, M10	30 mm	2.5 mm
HDI052	577039	47 - 52 mm	40	M8, M10	30 mm	2.5 mm
HDI058	577040	53 - 58 mm		M8, M10	30 mm	2.5 mm
HDI065	577041	60 - 65 mm	50	M8, M10	30 mm	2.5 mm
HDI078	577043	73 - 78 mm	65	M10, M12	30 mm	3 mm
HDI093	577045	88 - 93 mm	80	M10, M12	30 mm	3 mm
HDI116	577048	108 - 116 mm	100	M10, M12	30 mm	3 mm
HDI129	577050	124 - 129 mm		M10, M12	40 mm	4 mm
HDI145	577052	138 - 145 mm	125	M12, M16	40 mm	4 mm
HDI162	577054	156 - 162 mm		M12, M16	40 mm	4 mm
HDI171	577055	165 - 171 mm	150	M12, M16	40 mm	4 mm
HDI203	577058	196 - 203 mm		M12, M16	40 mm	4 mm
HDI225	577061	219 - 225 mm	200	M16, M20	40 mm	4 mm
HDI273	577066	265 - 273 mm	250	M16, M20	40 mm	4 mm
HDI316	577067	305 - 316 mm		M16, M20	40 mm	4 mm

Table 2/2


Catalog Number	Article Number	Screw Diameter (Sc)	Screw Diameter metric (Sc)	Screw Length (L)	Static Load
HDI018	577033	6 mm	M6	30mm	2000N
HDI023	577034	6 mm	M6	30mm	2000N
HDI028	577035	6 mm	M6	30mm	2000N
HDI037	577037	6 mm	M6	30mm	2000N
HDI045	577038	6 mm	M6	30mm	2000N
HDI052	577039	6 mm	M6	30mm	2000N
HDI058	577040	6 mm	M6	30mm	2000N
HDI065	577041	8 mm	M8	40mm	2000N
HDI078	577043	8 mm	M8	40mm	3500N
HDI093	577045	8 mm	M8	40mm	3500N
HDI116	577048	8 mm	M8	40mm	3500N
HDI129	577050	8 mm	M8	40mm	3500N
HDI145	577052	10 mm	M10	40mm	5000N
HDI162	577054	10 mm	M10	40mm	5000N
HDI171	577055	10 mm	M10	40mm	5000N
HDI203	577058	10 mm	M10	40mm	5000N
HDI225	577061	12 mm	M12	40mm	10000N
HDI273	577066	12 mm	M12	40mm	10000N

Catalog Number	Article Number	Screw Diameter (Sc)	Screw Diameter metric (Sc)	Screw Length (L)	Static Load
HDI316	577067	12 mm	M12	40mm	10000N

ADDITIONAL PRODUCT DETAILS

Lining is EPDM rubber.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

