

# nVent CADDY Speed Link Catenary Cable Spool



## FEATURES

Used for installing custom lengths of catenary cable with two locking devices

Spool with nVent CADDY Speed Link steel wire

Wire rope constructed from 7 bundles of 19 strands each of steel aircraft wire

## SPECIFICATIONS

**Finish:** Hot-Dip Galvanized

**Material:** Steel

Table 1/1

| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | Angle (a) |
|----------------|----------------|--------------------|------------------|-----------|
| SLC6CTO        | 196819         | 6 mm               |                  | 60 ° Max  |
| SLC6L50        | 196821         | 6 mm               | 50m              | 60 ° Max  |

## ADDITIONAL PRODUCT DETAILS


Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

Preload of the wire rope must be applied using Catenary Tensioning Tool.

Cut-to-order (CTO) lengths orderable in meter increments.

| Horizontal Intallation |        |        |
|------------------------|--------|--------|
| Preload                | 1000 N | 450 N  |
| Static Load 1 (F1)     | 490 N  | 590 N  |
| Static Load 2 (F2)     | 880 N  | 1080 N |
| Static Load 3 (F3)     | 980 N  | 1180 N |
| Vertical Installation  |        |        |
| Static Load 4 (F4)     | 4440 N |        |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

