

PBF Two Hole Base Plate for Threaded Rod



FEATURES

Light duty with two holes and one nut/adapter

SPECIFICATIONS

Finish: Electrogalvanized


Material: Steel


| Table 1/2 | | | | | | | |
|-------------------|----------------|---------------|------------|-----------|---------------|-------|--|
| Catalog Number | Article Number | Rod Size (RS) | Length (L) | Width (W) | Thickness (T) | A | |
| PBRM10L80 | 587135 | 10 | 80mm | 30 mm | 3 mm | 50 mm | |
| PBRM8M10L80 | 587145 | 8, 10 | 80mm | 30 mm | 3 mm | 50 mm | |
| PBRM12L120 | 587165 | 12 | 120mm | 40 mm | 4 mm | 81 mm | |
| PBRM8M10L12 0 | 587140 | 8, 10 | 120mm | 40 mm | 4 mm | 81 mm | |
| PBRM10L120 | 587160 | 10 | 120mm | 40 mm | 4 mm | 81 mm | |

| Table 2/2 | | | | | | |
|----------------|----------------|---|---|--|--|--|
| Catalog Number | Article Number | В | С | | | |

| PBRM10L80 | 587135 | 18 mm | 9 mm |
|--------------|--------|-------|-------|
| PBRM8M10L80 | 587145 | 18 mm | 9 mm |
| PBRM12L120 | 587165 | 18 mm | 11 mm |
| PBRM8M10L120 | 587140 | 18 mm | 11 mm |
| PBRM10L120 | 587160 | 18 mm | 11 mm |

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.