

Conductor Sleeve

Data Solutions



FEATURES

Used to adapt a limited range of smaller size cables to a larger size nVent ERICO Cadweld Mold

Provides strength and stability on finely-stranded copper conductors

SPECIFICATIONS

Material: Copper

Table 1/1

Catalog Number	Article Number	Finish	Type	Length (L)	Thickness (T)	Diameter (Ø)
S429F2J16		Tinned	Flared	25.4mm	0.51mm	12.19mm
S429F2N16		Tinned	Flared	25.4mm	0.51mm	13.72mm
B112		Tinned	Straight	26.99mm	0.79mm	5.38mm
B1331K		Tinned	Straight	25.4mm	0.79mm	3.56mm
PBS24F		Tinned	Flared	38.1mm	0.79mm	20.19mm

CatalogNumber	Article Number	Finish	Type	Length (L)	Thickness (T)	Diameter (Ø)
S02F		Tinned	Flared	25.4mm	0.79mm	15.52mm
S03F		Tinned	Flared	25.4mm	0.79mm	11.56mm
S05F		Tinned	Flared	25.4mm	0.79mm	9.93mm
S07F		Tinned	Flared	25.4mm	0.79mm	17.04mm
S17F		Tinned	Flared	25.4mm	0.79mm	8.74mm
S429F3S20		Tinned	Flared	31.75mm	0.64mm	23.62mm
H101	180140		Straight	26mm	1mm	6mm
H102	180170		Straight	25mm	1.05mm	4.3mm
H102F	180390		Flared	26mm	1.05mm	4.3mm
H105	180230		Straight	23.5mm	1mm	3mm
H106AF	180260		Flared	35mm	1mm	15mm
H106F	180250		Flared	26mm	1mm	15mm
H113F	180360		Flared	26mm	1mm	8mm
H117	180430		Straight	25mm	1mm	7mm
H103	180180		Straight	25mm	1.2mm	5.3mm
180380	180380	Tinned	Flared	25mm	2.4mm	5.3mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE