


Disconnecting Link

Data Solutions



FEATURES

Allows for quick and easy disconnection of the earthing system to facilitate testing of the earth in isolation

High conductivity, hard drawn, electrolytic tough pitch copper per EN 13601

Includes halogen-free polyamide insulators, stainless steel (EN 1.4401) hardware and mounting brackets

SPECIFICATIONS

Material: Copper

Complies With: IEC® EN 62561-1:2017 Class H

Table 1/2

Catalog Number	Finish	Thread Size (TS)	Height (H)	Width 1 (W1)	Width 2 (W2)	Thickness (T)
DLINKT	Tinned	M10	90mm	100mm	50mm	6mm
DLINKC	Bare	M10	90mm	100mm	50mm	6mm

Table 2/2


Catalog Number	Unit Weight
DLINKT	0.77kg

Catalog Number	Unit Weight
DLINKC	0.77kg

ADDITIONAL PRODUCT DETAILS

Tinned finish is 8 microns according to ASTM B545 Service Class "C" for corrosive environments.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE