

# Outdoor Comline FTTX Cabinet

## Data Solutions



Telecom applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather, Vandalism and thereby ensuring operational continuity. nVent SCHROFF cabinets can be used as Dslam / Point of Presence / Zone pooling / FTTC / FTTH / MFG cabinets.

## CERTIFICATIONS



## FEATURES

Height dimensions without plinth (140 mm)

Single wall, lightweight aluminium cabinet

Insulated cabinet

IP 55

## SPECIFICATIONS

**Material:** Aluminum

Table 1/3

| Catalog Number | Product Type    | Product Family | Rack Height | Height | Width | Depth |
|----------------|-----------------|----------------|-------------|--------|-------|-------|
| 12349-007      | Outdoor Cabinet | Comline FTTX   | 12U         | 600mm  | 800mm | 600mm |

| CatalogNumber | Product Type    | Product Family | Rack Height | Height | Width | Depth |
|---------------|-----------------|----------------|-------------|--------|-------|-------|
| 12349-006     | Outdoor Cabinet | Comline FTTX   | 25U         | 1200mm | 800mm | 600mm |
| 12349-005     | Outdoor Cabinet | Comline FTTX   | 12U         | 600mm  | 800mm | 600mm |
| 12349-008     | Outdoor Cabinet | Comline FTTX   | 25U         | 1200mm | 800mm | 600mm |

| Table 2/3      |               |             |             |            |               |                                                                                                   |
|----------------|---------------|-------------|-------------|------------|---------------|---------------------------------------------------------------------------------------------------|
| Catalog Number | Wall Type     | Door Type   | Access      | Cooling    | EMC Shielding | Complies With                                                                                     |
| 12349-007      | Single Walled | Single Door | Front, Back | Insulation | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-006      | Single Walled | Single Door | Front, Back | Insulation | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-005      | Single Walled | Single Door | Front, Back | Insulation | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-008      | Single Walled | Single Door | Front, Back | Insulation | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |

| Table 3/3      |                  |        |
|----------------|------------------|--------|
| Catalog Number | Package Quantity | Finish |

|           |   |               |
|-----------|---|---------------|
| 12349-007 | 1 | Powder Coated |
| 12349-006 | 1 | Powder Coated |
| 12349-005 | 1 | Powder Coated |
| 12349-008 | 1 | Powder Coated |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**