

Connection clamp with levers

Distribution Clamps for Distribution Box.



FEATURES

Connection clamp with levers

For all conductor types

3 or 5 conductors

Up to 4.00 mm²

SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Color	Ambient Temperature	Clamp Quantity	Depth	Height
20118-902	Clamp	Transparent, Green	85°C max	3	18.8mm	8.4mm
20118-903	Clamp	Transparent, Green	85°C max	5	18.8mm	8.4mm

Table 2/3

Catalog Number	Material	Max Current	Max Voltage	Package Quantity	Weight	Width
20118-902	Polycarbonate	20A	600V	10	2.5g	18.8mm
20118-903	Polycarbonate	20A	600V	10	4g	30mm

Table 3/3

Catalog Number	Quick Ship
----------------	------------

20118-902	No
20118-903	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE