nVent SCHROFF

We connect and protect

Panhead Screw, Torx, Steel Zinc Plated, Self-Securing Thread, M2.5 x 6 mm

CATALOG NUMBER

24560-159

Pan head torx screws with different metric threads and lengths. With optional features like GND earthing function or self-securing thread.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

Pan Head Screw with torx, self-locking

PRODUCT ATTRIBUTES

Length: 6mm
Finish: Zinc Plated
Package Quantity: 100
Thread Size: M2.5
Material: Steel
Product Type: Screw
Type: Panhead Screw
Works With: Backplanes; Test Adapters

ADDITIONAL PRODUCT DETAILS

Torque max. 0.2 Nm.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.