


# nVent CADDY Cat CM U-Hook



## CERTIFICATIONS



## FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

System offers a convenient pathway for wires and cables

Specially designed U-Hooks have large-diameter, rounded support surfaces

U-Hooks can be mounted vertically along the same drop rod to create a tree configuration

Cantilever mounting allows U-Hooks to be mounted to walls and columns with brackets

Rounded edges help prevent over-bending and kinking of cables

Ideal for retrofit applications where cable runs need to be routed around existing building infrastructure

Compliant with NEC® and ANSI®/TIA structured cabling systems standards

## SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Steel

Table 1/2


| Catalog Number | Cable Capacity, Cat 5e | Cable Capacity, Cat 6 | Cable Capacity, Cat 6A | A | Area | Hole Size (HS) |
|----------------|------------------------|-----------------------|------------------------|---|------|----------------|
|----------------|------------------------|-----------------------|------------------------|---|------|----------------|

|            |     |     |     |        |                    |        |
|------------|-----|-----|-----|--------|--------------------|--------|
| CAT300CMLN | 700 | 525 | 325 | 304 mm | 812mm <sup>2</sup> | 9.5 mm |
| CAT200CMLN | 450 | 350 | 215 | 203 mm | 533mm <sup>2</sup> | 9.5 mm |

Table 2/2

| Catalog Number | Static Load |
|----------------|-------------|
| CAT300CMLN     | 440N        |
| CAT200CMLN     | 440N        |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

