

Rail Jumper Bond, Power, W Style



FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

Easy installation, with minimum installer training required

Simple and highly-portable installation equipment

Equally usable on old, worn, or new rails

Highly durable

SPECIFICATIONS


Bond Terminal Style: W

Table 1/1

Catalog Number	Insulated	Material	Finish	Conductor Size	Length (L)	Diameter (Ø)
PBW12J72B	No	Copper	Bare, Tinned	2/0 Ropelay	1828.8mm	12.04 mm
PBW12Q42B	No	Copper	Bare, Tinned	4/0 Concentric	1066.8mm	13.41 mm
PBW12Q48B	No	Copper	Bare, Tinned	4/0 Concentric	1219.2mm	13.41 mm
PBW12S56B	No	Copper	Bare, Tinned	4/0 Ropelay	1422.4mm	15.21 mm

CatalogNumber	Insulated	Material	Finish	Conductor Size	Length (L)	Diameter (Ø)
PBW12W14B	No	Copper	Bare, Tinned	250 kcmil Ropelay	355.6mm	16.59 mm
PBW12W48B	NoEFS_PBW12 W48B	Copper	Bare, Tinned	250 kcmil Ropelay	1219.2mm	16.59 mm
PBW12W54B	No	Copper	Bare, Tinned	250 kcmil Ropelay	1371.6mm	16.59 mm
PBW12W55B	No	Copper	Bare, Tinned	250 kcmil Ropelay	1397mm	16.59 mm
PBW13S36B	No	Copper, Steel	Bare, Copper Plated	500 kcmil Ropelay	914.4mm	23.42 mm
PBW13S66B	No	Copper, Steel	Bare, Copper Plated	500 kcmil Ropelay	1676.4mm	23.42 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE