

Concept Swing-Out Panels



Panels swing clear from the front of the enclosure to provide access to mounted internal equipment. For CSPB panels, maximum swing is 94 degrees. For CSP panels, maximum panel swing is 106 degrees. Distance from panel surface to door when in the latched position is 1.71 in. (43 mm) for solid doors and 1.45 in. (37 mm) for window doors. Kits include panel, brackets and hardware to mount to the front flange. Swing-out panels also can be mounted on front-to-back adjustable rails. CSPB panels require adapter CSPBADB and front-to-back adjustable rails for front-to-back adjustment.

FEATURES

CSPB panels, maximum swing is 94 degrees

CSP panels, maximum panel swing is 106 degrees

Distance from panel surface to door when in the latched position is 1.71 in. (43 mm) for solid doors and 1.45 in. (37 mm) for window doors

Kits include panel, brackets and hardware to mount to the front flange

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Material	Finish	Color
CSP1212	11960	248mm	249mm	Mild Steel	Powder Coated	White
CSPB1212	16487	247mm	247mm	Mild Steel	Powder Coated	White
CSP1612	11970	350mm	249mm	Mild Steel	Powder Coated	White
CSPB1612	16488	348mm	247mm	Mild Steel	Powder Coated	White
CSPB1616	16491	348mm	349mm	Mild Steel	Powder Coated	White
CSP1616	11990	350mm	351mm	Mild Steel	Powder Coated	White
CSPB1620	16492	348mm	450mm	Mild Steel	Powder Coated	White
CSP1620	12300	350mm	453mm	Mild Steel	Powder Coated	White
CSPB2016	16493	450mm	349mm	Mild Steel	Powder Coated	White
CSP2016	12000	452mm	351mm	Mild Steel	Powder Coated	White
CSP2020	12280	452mm	453mm	Mild Steel	Powder Coated	White
CSPB2020	16494	450mm	450mm	Mild Steel	Powder Coated	White
CSPB2024	16718	450mm	552mm	Mild Steel	Powder Coated	White
CSP2024	12400	452mm	554mm	Mild Steel	Powder Coated	White
CSPB2416	16495	552mm	348mm	Mild Steel	Powder Coated	White
CSP2416	12290	553mm	351mm	Mild Steel	Powder Coated	White
CSPB2420	16496	552mm	450mm	Mild Steel	Powder Coated	White
CSP2420	12370	553mm	453mm	Mild Steel	Powder Coated	White
CSPB2424	16497	552mm	552mm	Mild Steel	Powder Coated	White

Catalog Number	Article Number	Height	Width	Material	Finish	Color
CSP2424	12380	553mm	554mm	Mild Steel	Powder Coated	White
CSPB2430	16498	552mm	704mm	Mild Steel	Powder Coated	White
CSPB3020	16501	704mm	450mm	Mild Steel	Powder Coated	White
CSP3020	12390	706mm	453mm	Mild Steel	Powder Coated	White
CSPB3024	16502	704mm	552mm	Mild Steel	Powder Coated	White
CSP3024	12440	706mm	554mm	Mild Steel	Powder Coated	White
CSP3030	12490	706mm	707mm	Mild Steel	Powder Coated	White
CSPB3030	16503	704mm	704mm	Mild Steel	Powder Coated	White
CSPB3624	16504	856mm	552mm	Mild Steel	Powder Coated	White
CSP3624	12480	858mm	554mm	Mild Steel	Powder Coated	White
CSPB3630	16505	856mm	704mm	Mild Steel	Powder Coated	White
CSP3630	12500	858mm	707mm	Mild Steel	Powder Coated	White
CSP3636	12550	858mm	859mm	Mild Steel	Powder Coated	White
CSPB3636	16506	856mm	857mm	Mild Steel	Powder Coated	White
CSPB4824	16508	1161mm	552mm	Mild Steel	Powder Coated	White
CSPB4236	16507	1009mm	857mm	Mild Steel	Powder Coated	White
CSPB4836	16511	1161mm	857mm	Mild Steel	Powder Coated	White
CSPB6036	16512	1466mm	857mm	Mild Steel	Powder Coated	White

ADDITIONAL PRODUCT DETAILS

Swing-out panels also can be mounted on front-to-back adjustable rails. CSPB panels require adapter CSPBADB and front-to-back adjustable rails for front-to-back adjustment.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte