

Elbow 45-Degree Lay-in Painted



Lay-in Painted 45-Degree Elbows are used for continuous run with 45-degree turns. Top and inside covers removable so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system.

FEATURES

Lay-in Painted 45-Degree Elbows are used for continuous run with 45-degree turns

Top and inside covers removable so wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

SPECIFICATIONS

Color Code: ANSI 61
Color: Gray
Material: Mild Steel
Finish: Powder Coated

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F22G45E	52080	Elbow	64mm	64mm	1.52mm	No
F1010G45E	45690	Elbow	254mm	254mm	1.9mm	No
F1212G45E	51910	Elbow	305mm	305mm	1.9mm	No
F33G45E	15487	Elbow	76mm	76mm	1.52mm	No
F44G45E	52240	Elbow	102mm	102mm	1.52mm	No
F66G45E	52410	Elbow	152mm	152mm	1.52mm	No
F88G45E	52670	Elbow	203mm	203mm	1.9mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE