

Elbow 90-Degree Outside Opening



Lay-in Painted 90-Degree Elbows with Outside Opening are used for continuous run with 90-degree turns. Top, bottom and outside covers removable. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system.

FEATURES

Lay-in Painted 90-Degree Elbows with Outside Opening are used for continuous run with 90-degree turns

Top, bottom and outside covers removable

Lay-in feature allows wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

SPECIFICATIONS

Color Code: ANSI 61
Color: Gray
Material: Mild Steel
Finish: Powder Coated

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F121290EOUT	13156	Elbow	64mm	64mm	1.9mm	No
F8890EOUT	13154	Elbow	64mm	64mm	1.9mm	No
F2290EOUT	13151	Elbow	64mm	64mm	1.52mm	No
F4490EOUT	13152	Elbow	64mm	64mm	1.52mm	No
F101090EOUT	13155	Elbow	64mm	64mm	1.9mm	No
F6690EOUT	13153	Elbow	64mm	64mm	1.52mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE