

Panels for Junction Box



Use these panels in Junction Boxes. Available in various materials to meet various application requirements. Stainless steel and aluminum panels are protected on one side with a plastic film.

FEATURES

Panel mounting hardware is furnished with all enclosures which accept these panels

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Material	Finish	Color
A10P8AL	55650	222mm	171mm	Aluminum	Anodized	
A10P10AL	17381	171mm	174mm	Aluminum	Anodized	
A12P10AL	55660	273mm	222mm	Aluminum	Anodized	
A14P12AL	55670	324mm	273mm	Aluminum	Anodized	
A16P14AL	55680	375mm	327mm	Aluminum	Anodized	
A18P16AL	58500	425mm	377mm	Aluminum	Anodized	
A20P16JAL	32876	476mm	377mm	Aluminum	Anodized	
A6P4AL	55620	124mm	73mm	Aluminum	Anodized	
A6P6AL	55630	124mm	123mm	Aluminum	Anodized	
A8P6AL	55640	171mm	123mm	Aluminum	Anodized	
A8P8AL	17378	222mm	225mm	Aluminum	Anodized	
A4P4G	21494	73mm	73mm	Mild Steel	Galvanized	
A6P4	54750	124mm	73mm	Mild Steel	Powder Coated	White
A6P4G	26049	124mm	73mm	Mild Steel	Galvanized	
A6P4SS	55550	124mm	73mm	Stainless Steel 304	Brushed #3	
A6P6SS	55560	124mm	123mm	Stainless Steel 304	Brushed #3	
A6P6	54760	124mm	123mm	Mild Steel	Powder Coated	White
A6P6G	26059	124mm	123mm	Mild Steel	Galvanized	
A8P6	54770	171mm	123mm	Mild Steel	Powder Coated	White

Catalog Number	Article Number	Height	Width	Material	Finish	Color
A8P6SS	55570	171mm	123mm	Stainless Steel 304	Brushed #3	
A9P6G	21495	187mm	117mm	Mild Steel	Galvanized	
A7P7G	23796	149mm	149mm	Mild Steel	Galvanized	
A8P6G	26069	171mm	123mm	Mild Steel	Galvanized	
A8P8	54820	171mm	174mm	Mild Steel	Powder Coated	White
A8P8G	17447	171mm	174mm	Mild Steel	Galvanized	
A12P6	54950	273mm	123mm	Mild Steel	Powder Coated	White
A12P6G	15142	273mm	123mm	Mild Steel	Galvanized	
A10P8	54780	222mm	174mm	Mild Steel	Powder Coated	White
A10P8SS	55580	222mm	171mm	Stainless Steel 304	Brushed #3	
A10P8G	26079	222mm	174mm	Mild Steel	Galvanized	
A10P10	54830	222mm	225mm	Mild Steel	Powder Coated	White
A10P10G	15141	222mm	225mm	Mild Steel	Galvanized	
A12P10	54790	273mm	225mm	Mild Steel	Powder Coated	White
A14P8	54000	324mm	174mm	Mild Steel	Powder Coated	White
A14P8G	15143	324mm	174mm	Mild Steel	Galvanized	
A12P10G	26089	273mm	225mm	Mild Steel	Galvanized	
A12P10SS	55590	273mm	222mm	Stainless Steel 304	Brushed #3	
A12P12G	15312	273mm	276mm	Mild Steel	Galvanized	
A12P12	54840	273mm	276mm	Mild Steel	Powder Coated	White

Catalog Number	Article Number	Height	Width	Material	Finish	Color
A12P12SS	55490	273mm	273mm	Stainless Steel 304	Brushed #3	
A14P12	54800	324mm	276mm	Mild Steel	Powder Coated	White
A14P12G	26099	324mm	276mm	Mild Steel	Galvanized	
A14P12SS	55600	324mm	273mm	Stainless Steel 304	Brushed #3	
A16P10	54270	375mm	225mm	Mild Steel	Powder Coated	White
A16P10G	15145	375mm	225mm	Mild Steel	Galvanized	
A16P14	54810	375mm	327mm	Mild Steel	Powder Coated	White
A16P14G	26109	375mm	327mm	Mild Steel	Galvanized	
A16P14SS	55610	375mm	327mm	Stainless Steel 304	Brushed #3	
A18P16	58480	425mm	377mm	Mild Steel	Powder Coated	White
A18P16G	26119	425mm	377mm	Mild Steel	Galvanized	
A18P16SS	58490	425mm	377mm	Stainless Steel 304	Brushed #3	
A20P16J	32875	476mm	377mm	Mild Steel	Powder Coated	White

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE