

## ProLine Solid Sides



Solid Sides close the open sides of an enclosure frame and attach to the enclosure frame with semi-flush screws. Hangers are included for easy alignment of screws. Sides have two grounding studs and a foam-in-place gasket. Mounting hardware is included. Solid Sides are not suitable as barriers between joined enclosures.

### FEATURES

---

Solid Sides are finished with paint over plated surfaces

## SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
PSS146	96130	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS146SS	31709	Stainless Steel 304	Brushed			1.52mm
PSS148	96140	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS148SS	31719	Stainless Steel 304	Brushed			1.52mm
PSS145	96120	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS164	96150	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS166	96170	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS166SS	31729	Stainless Steel 304	Brushed			1.52mm
PSS168SS	31739	Stainless Steel 304	Brushed			1.52mm
PSS168	96180	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS185	96210	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS186	96220	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS186SS	31749	Stainless Steel 304	Brushed			1.52mm
PSS188SS	31759	Stainless Steel 304	Brushed			1.52mm
PSS188	96230	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS184	96200	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS205	96260	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS206	96270	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS206SS	31769	Stainless Steel 304	Brushed			1.52mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
PSS208	96280	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS208SS	31779	Stainless Steel 304	Brushed			1.52mm
PSS204	96250	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS225	90730	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS226	96300	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS228	96310	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS228SS	31799	Stainless Steel 304	Brushed			1.52mm
PSS76SS	31699	Stainless Steel 304	Brushed			1.52mm
PSS76	96110	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS125	30438	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS145HF2	11459	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS146HF2	11469	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS148HF2	11479	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS164HF2	11489	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS165	96160	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS165HF2	11499	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS184HF2	11539	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS186HF2	11559	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS188HF2	11569	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS204HF2	11589	Mild Steel		Light Gray	RAL 7035	1.52mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
PSS206HF2	11609	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS208HF2	11619	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS225HF2	16959	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS228HF2	11649	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS76HF2	11449	Mild Steel		Light Gray	RAL 7035	1.52mm
PSS209	96290	Mild Steel		Light Gray	RAL 7035	1.9mm
PSS229	96320	Mild Steel		Light Gray	RAL 7035	1.9mm
PSS209HF2	11629	Mild Steel		Light Gray	RAL 7035	1.9mm
PSS229HF2	11659	Mild Steel		Light Gray	RAL 7035	1.9mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**