

Straight Section Lay-in Painted Galvanized Hinged-Cover



Lay-in Painted Galvanized Hinged-Cover Type 3R Straight Sections are used for enclosing wire and cable in wireway runs.

FEATURES

Lay-in Painted Galvanized Hinged-Cover Type 3R Straight Sections are used for enclosing wire and cable in wireway runs

SPECIFICATIONS

Color Code: ANSI 61
Finish: Galvanized; Powder Coated
Color: Gray
Material: Mild Steel

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Depth	Thickness
F44T3R12	43489	Straight Section	102mm	102mm	305mm	1.52mm
F44T3R120	43529	Straight Section	102mm	102mm	3048mm	1.52mm
F44T3R60	43509	Straight Section	102mm	102mm	1524mm	1.52mm
F66T3R12	43639	Straight Section	152mm	152mm	305mm	1.52mm
F66T3R120	43679	Straight Section	152mm	152mm	3048mm	1.52mm
F66T3R60	43659	Straight Section	152mm	152mm	1524mm	1.52mm
F88T3R12	43799	Straight Section	203mm	203mm	305mm	1.9mm
F88T3R120	43839	Straight Section	203mm	203mm	3048mm	1.9mm
F88T3R60	43819	Straight Section	203mm	203mm	1524mm	1.9mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE