

Universal Free-Stand Flat End Plate Stainless Steel



Flat End plate is used to seal open side(s) of Universal Free-Stand Enclosures. The Flat End Plate provides a low profile cover and is Type 4X, 4, 12, 3R, and IP66 rated. Studs welded to the end plate eliminate bolt holes. Gasket and mounting hardware are furnished.

FEATURES

Universal Free-Stand Flat End plate is used to seal open side(s) of nVent HOFFMAN Universal Free-Stand Enclosures.

The Flat End Plate provides a low profile cover and is Type 4X, 4, 12, 3R, and IP66 rated

Studs welded to the end plate eliminate bolt holes

Gasket and mounting hardware are furnished

SPECIFICATIONS

Finish: Brushed
Material: Stainless Steel 304

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Thickness	Quick Ship
AU7218FEPSS	38977	1832mm	460mm	7mm	1.9mm	No
AU8424FEPSS	38975	2137mm	613mm	7mm	1.9mm	No
AU8418FEPSS	38976	2137mm	460mm	7mm	1.9mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE