

19" Pusher Fan, 2 U, Axial

Power Utilities

Fan tray with integrated pusher fan.



CERTIFICATIONS



FEATURES

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to sub racks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage AC	Input Voltage DC
10713-526	230 V min	
10713-518	230 V min	

Catalog Number	Input Voltage AC	Input Voltage DC
10713-536	115 V min	
10713-520	115 V min	
10713-534	230 V min	
10713-529		24 V min
10713-537		24 V min
19713-540		

ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE