

# RackPower PDU, RP2xxx, 120 VAC, 1-phase

## Power Utilities

Modular, compact intelligent PDU with inlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

### FEATURES

RackPower RP2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 100 - 120 VAC, 1-phase L-N

Connecting cable 10", with NEMA L5 connector

Nema L5 outlets

User-defined power-on time delay or automatic power-on sequencing

### SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Color	Length	Voltage AC	Function
RP2310	Socket Strip	NEMA 5-20R	Black	917 mm	120 V	Input Monitored, Switched Outlets
RP2319	Socket Strip	NEMA 5-20R	Black	1490 mm	120 V	Input Monitored, Switched Outlets

Table 2/2

Catalog Number	Depth	Width
RP2310	53 mm	52 mm
RP2319	53 mm	52 mm

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE