

Varistar CP Top Rear Panel, Shortened

Power Utilities

Shortened Rear Panel available for IP20, IP55 applications.

Shortened rear panels ensure efficient cable management.

FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Height of connection plate 400 mm

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Color	Color Code	Product Type
21630-360	38 U	1800 mm	600 mm	Black Grey	RAL 7021	Cabinet Door
21630-361	38 U	1800 mm	800 mm	Black Grey	RAL 7021	Cabinet Door
21630-362	42 U	2000 mm	600 mm	Black Grey	RAL 7021	Cabinet Door
21630-363	42 U	2000 mm	800 mm	Black Grey	RAL 7021	Cabinet Door
21630-364	47 U	2200 mm	600 mm	Black Grey	RAL 7021	Cabinet Door
21630-365	47 U	2200 mm	800 mm	Black Grey	RAL 7021	Cabinet Door

Table 2/2

Catalog Number	Protection Rating
21630-360	IP55
21630-361	IP55

Catalog Number	Protection Rating
21630-362	IP55
21630-363	IP55
21630-364	IP55
21630-365	IP55

ADDITIONAL PRODUCT DETAILS

The height of the rear panel is 400 mm less than the cabinet height to accommodate the connecting plate.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE