

920 Series, Solid-State Relay



RAYCHEM 920 Series - SSR provides electronic switching capability for heat trace circuits. Available in 1-,2-, or 3-pole solid-state, normally open relay , 277V or 600V, and 30A or 60A at 104°F (40°C). Allows for proportional, power limiting, and soft start control algorithms.

FEATURES

- Easy to install
- Suitable for Class I Div. 2/Zone 2 hazardous locations
- Infinite Life Cycle

SPECIFICATIONS

Table 1/1			
Catalog Number	Item Name	Voltage Rating	Current Rating
10260-008	SS3	277 V max	30 A
10260-009	SSH3	600 V max	30 A
10260-011	SSH6	600 V max	60 A

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT