

# Splice or Tee Connection Kit, Cold Applied



nVent RAYCHEM T-100 is a cold-applied high profile splice or tee connection kit for trace heating cables in both non-hazardous and hazardous locations. Mounted on the pipe, through the thermal insulation and cladding. Includes cold-applied heating cable core sealer.

## FEATURES

Simple and fast to install and test

Cold-applied: no heat gun or hot work permit required, re-enterable

High performance: resistant to impact, high temperature, chemicals and UV

Reliable during long life: 10 year product warranty available, maintenance free

## SPECIFICATIONS

Table 1/4

| Catalog Number | Item Name | Material                       | Mounting | Voltage Rating for FM, CSA | Voltage Rating for PTB | Current Rating for FM, CSA |
|----------------|-----------|--------------------------------|----------|----------------------------|------------------------|----------------------------|
| 447379-000     | T-100     | Glass Fiber Reinforced Polymer | On Pipe  | 277 V                      | 480 V                  | 50 A                       |

Table 2/4

| Catalog Number | Item Name | Current Rating for PTB | IP Rating | NEMA Rating | Ambient Temperature | Cover Included |
|----------------|-----------|------------------------|-----------|-------------|---------------------|----------------|
| 447379-000     | T-100     | 40 A                   | IP67      | 4X          | -55 to 260 °C       | Yes            |

Table 3/4

| Catalog Number | Item Name | For Ex-Zone Gas | For Ex-Zone Dust | Length | Height | Width  |
|----------------|-----------|-----------------|------------------|--------|--------|--------|
| 447379-000     | T-100     | 1, 2            | 21, 22           | 120 mm | 240 mm | 120 mm |

Table 4/4

| Catalog Number | Item Name | Depth |
|----------------|-----------|-------|
| 447379-000     | T-100     | 90 mm |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

Tel +1.800.545.6258  
Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latin America

Tel +1.713.868.4800  
Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM** **PYROTENAX** **TRACER** **NUHEAT**