

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



CERTIFICATIONS



FEATURES

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized; Passivated

EMC Shielding: No
Product Type: Subrack/Chassis

Table 1/3

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	Shock and Vibration Tolerance
24567-161	3U	175mm	1	Backplane	160mm	5g (force)
24567-162	3U	235mm	1	Backplane	160mm, 220mm	5g (force)
24567-163	3U	295mm	1	Backplane	160mm, 220mm, 280mm	5g (force)
24567-164	3U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	5g (force)
24567-461	6U	175mm	1	Backplane	160mm	5g (force)
24567-462	6U	235mm	1	Backplane	160mm, 220mm	5g (force)
24567-463	6U	295mm	1	Backplane	160mm, 220mm, 280mm	5g (force)
24567-464	6U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	5g (force)

Table 2/3

Catalog Number	Handle Included	Mounting	Complies With	Rack Width	Static Load	Certifications
24567-161	Yes	Rack	IEC 60297-3-103	84HP	15kg	RoHS
24567-162	Yes	Rack	IEC 60297-3-103	84HP	15kg	RoHS, DB
24567-163	Yes	Rack	IEC 60297-3-103	84HP	15kg	DB, RoHS
24567-164	Yes	Rack	IEC 60297-3-103	84HP	15kg	RoHS, DB
24567-461	Yes	Rack	IEC 60297-3-103	84HP	15kg	RoHS, DB

CatalogNumber	HandleIncluded	Mounting	Complies With	Rack Width	Static Load	Certifications
24567-462	Yes	Rack	IEC 60297-3-103	84HP	15kg	DB, RoHS
24567-463	Yes	Rack	IEC 60297-3-103	84HP	15kg	RoHS, DB
24567-464	Yes	Rack	IEC 60297-3-103	84HP	15kg	DB, RoHS

Table 3/3

Catalog Number	Quick Ship
24567-161	No
24567-162	No
24567-163	No
24567-164	No
24567-461	No
24567-462	No
24567-463	No
24567-464	No

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE