

Universal Restraint Clip



CERTIFICATIONS











FEATURES

Attaches cable brace to structure

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/1						
Catalog Number	Article Number	Brace Size	Hole Size (HS)	Thickness (T)	UL Listed Load	
CSBURC38	402198	#12, #18, #36	11 mm	4.27 mm	3430N	
CSBURC58	402200	#12, #18, #36	17 mm	4.27 mm	3430N	
CSBURC12	402199	#12, #18, #36	14 mm	4.27 mm	3430N	


ADDITIONAL PRODUCT DETAILS

Brace member is not included.

Mount to the structure using the center hole. Loop cable through the holes in the bent tabs and swage in place.

UL Loads				
Part Number	Brace Member	Load Rating		
	CSB12CBL	1859 N		
CSBURC38	CSB18CBL	3434 N		
	CSB36CBL	8492 N		
	CSB12CBL	1859 N		
CSBURC12	CSB18CBL	3434 N		
	CSB36CBL	8492 N		
	CSB12CBL	1859 N		
CSBURC58	CSB18CBL	3434 N		
	CSB36CBL	8492 N		

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

