

Fusion G7 Full-Height Side Panel



Galvanized steel full-height side panels.

FEATURES

Panel mounting hardware is furnished with the panel

SPECIFICATIONS

Finish: Galvanized

Material: Mild Steel

Table 1/1

Catalog Number	Height	Width	Thickness	Fits Frame	Quick Ship
FUMP1025G020S	955mm	193mm	1.5mm	1000 x 250mm	No
FUMP1030G020S	955mm	241mm	1.5mm	1000 x 300mm	No
FUMP1040G020S	955mm	342mm	1.5mm	1000 x 400mm	No
FUMP1230G020S	1156mm	241mm	1.5mm	1200 x 300mm	No
FUMP1232G020S	1156mm	266mm	1.5mm	1200 x 325mm	No
FUMP1240G020S	1156mm	342mm	1.5mm	1200 x 400mm	No
FUMP1532G020S	1455mm	266mm	1.5mm	1500 x 325mm	No
FUMP1542G020S	1455mm	365mm	1.5mm	1500 x 425mm	No
FUMP3015G020S	254mm	91mm	1.5mm	300 x 150mm	No
FUMP3020G020S	254mm	142mm	1.5mm	300 x 200mm	No
FUMP3022G020S	254mm	167mm	1.5mm	300 x 225mm	No
FUMP4015G020S	356mm	91mm	1.5mm	400 x 150mm	No
FUMP4022G020S	356mm	167mm	1.5mm	400 x 225mm	No
FUMP5022G020S	455mm	167mm	1.5mm	500 x 225mm	No
FUMP5030G020S	455mm	241mm	1.5mm	500 x 300mm	No
FUMP6020G020S	556mm	142mm	1.5mm	600 x 200mm	No
FUMP6022G020S	556mm	167mm	1.5mm	600 x 225mm	No

Catalog Number	Height	Width	Thickness	Fits Frame	Quick Ship
FUMP6030G020S	556mm	241mm	1.5mm	600 x 300mm	No
FUMP6032G020S	556mm	266mm	1.5mm	600 x 325mm	No
FUMP6040G020S	556mm	342mm	1.5mm	600 x 400mm	No
FUMP7025G020S	655mm	193mm	1.5mm	700 x 250mm	No
FUMP8022G020S	754mm	167mm	1.5mm	800 x 225mm	No
FUMP8030G020S	754mm	241mm	1.5mm	800 x 300mm	No
FUMP8032G020S	754mm	266mm	1.5mm	800 x 325mm	No
FUMP8042G020S	754mm	365mm	1.5mm	800 x 425mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE