

## Fusion G7 Gland Plate



Provides a removable cable egress and entry plate while maintaining IP/UL/CSA integrity of the enclosure. Maintains IP55 or IP66/UL/CSA Type 4 and 12 when properly installed on a nVent HOFFMAN enclosure.

### FEATURES

---

Foam-in-place gasket, fasteners and instructions provided

## SPECIFICATIONS

|                    |               |
|--------------------|---------------|
| <b>Color:</b>      | Light Gray    |
| <b>Material:</b>   | Mild Steel    |
| <b>Finish:</b>     | Powder Coated |
| <b>Color Code:</b> | RAL 7035      |

Table 1/1

| Catalog Number | Thickness | Cutout Size | Quick Ship |
|----------------|-----------|-------------|------------|
| FUGP1815C500S  | 1.5mm     | 150 x 180mm | No         |
| FUGP2809C500S  | 1.5mm     | 90 x 280mm  | No         |
| FUGP2815C500S  | 1.5mm     | 150 x 280mm | No         |
| FUGP1809C500S  | 1.5mm     | 90 x 180mm  | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**