

# Inner Doors For Power Distribution, DI



Displays and indicators can be mounted on a surface within the enclosure while covering other components, and preventing unauthorized access.

## FEATURES

---

Description: Inner door provides a hinged mounting surface for equipment behind a standard or glazed front door. A mounting space of 80 mm, is available between the doors when the inner door is in the most forward position. Can be adjusted in depth by steps of 25 mm. The mounting plate remains usable behind the inner door. The door is equipped with two double-bit 3 mm locks.

Material: 1.5 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 door with mounting accessories.

SPECIFICATIONS

- Thickness:

1.5mm
- Color:

Light Gray
- Material:

Mild Steel
- Finish:

Powder Coated
- Color Code:

RAL 7035

| Table 1/1      |                |        |       |       |                    |                |
|----------------|----------------|--------|-------|-------|--------------------|----------------|
| Catalog Number | Article Number | Height | Width | Depth | Enclosure Material | Product Family |
| DI1206R5       |                | 1153mm | 565mm | 53mm  | Mild Steel         | Free-Standing  |
| DI1208R5       |                | 1153mm | 765mm | 53mm  | Mild Steel         | Free-Standing  |
| DI1406R5       | DI1406R5       | 1353mm | 565mm | 53mm  | Mild Steel         | Free-Standing  |
| DI1408R5       | DI1408R5       | 1353mm | 765mm | 53mm  | Mild Steel         | Free-Standing  |
| DI1606R5       | DI1606R5       | 1553mm | 565mm | 53mm  | Mild Steel         | Free-Standing  |
| DI1608R5       | DI1608R5       | 1553mm | 765mm | 53mm  | Mild Steel         | Free-Standing  |
| DI1806R5       | DI1806R5       | 1753mm | 565mm | 53mm  | Mild Steel         | Free-Standing  |
| DI1808R5       | DI1808R5       | 1753mm | 765mm | 53mm  | Mild Steel         | Free-Standing  |
| DI2006R5       | DI2006R5       | 1953mm | 565mm | 53mm  | Mild Steel         | Free-Standing  |
| DI2008R5       | DI2008R5       | 1953mm | 765mm | 53mm  | Mild Steel         | Free-Standing  |
| DI2206R5       | DI2206R5       | 2153mm | 565mm | 53mm  | Mild Steel         | Free-Standing  |
| DI2208R5       | DI2208R5       | 2153mm | 765mm | 53mm  | Mild Steel         | Free-Standing  |

ADDITIONAL PRODUCT DETAILS

Other sizes available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**