

Etsirack Frame



Welded frame with metric grid holes in accordance with ETS 300119-3, with load capacity of 200 kg.

CERTIFICATIONS



FEATURES

Welded frame with metric grid holes in accordance with ETS 300119-3

Mounting height 81 SU

Static load-carrying capacity 200 kg

Back-to-back row layout is possible

In accordance with standards IEC 48 D and ETS 300 119

Top mounted cabling frame

SPECIFICATIONS

Static Load:	200kg
Product Type:	Cabinet/Rack Frame
Material:	Steel
Frame Material:	Steel

Table 1/2

Catalog Number	Height	Width	Depth	Package Quantity	Color	Color Code
----------------	--------	-------	-------	------------------	-------	------------

10125-010	2200mm	600mm	300mm	1	Light Grey	RAL 7035
10125-011	2200mm	600mm	300mm	2	Light Grey	RAL 7035

Table 2/2			
Catalog Number	Finish	Type	Quick Ship
10125-010	Powder Coated	Standard	No
10125-011	Powder Coated	Standard	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE