

# EuropacPRO 19" Subrack Kit for DIN Connector, Slide Rail, Retrofit Shielding



Non-shielded subrack for Din Connector mounting EN 60603-2 , Subrack can be assembled on slide rails to support the subrack inside a cabinet.

## CERTIFICATIONS



## FEATURES

Subrack with side panel type F ("flexible"), 19" bracket with notch for slide rail assembly

Installed load up to 11 kg

Subrack can be used with slide rails

Horizontal rails, rear, for connector mounting (IEC 60603-2 / DIN 41612)

Threaded insert pre-fitted

## SPECIFICATIONS

|                       |                 |
|-----------------------|-----------------|
| <b>Static Load:</b>   | 11kg            |
| <b>EMC Shielding:</b> | No              |
| <b>Product Type:</b>  | Subrack/Chassis |

Table 1/3

| Catalog Number | Rack Height | Depth | Package Quantity | For Mounting | Board Depth | EMC Gasket Type |
|----------------|-------------|-------|------------------|--------------|-------------|-----------------|
|----------------|-------------|-------|------------------|--------------|-------------|-----------------|

|           |    |       |   |               |                                     |                 |
|-----------|----|-------|---|---------------|-------------------------------------|-----------------|
| 24553-192 | 3U | 235mm | 1 | DIN Connector | 160mm,<br>220mm                     | Stainless Steel |
| 24553-193 | 3U | 295mm | 1 | DIN Connector | 160mm,<br>220mm,<br>280mm           | Stainless Steel |
| 24553-194 | 3U | 355mm | 1 | DIN Connector | 160mm,<br>220mm,<br>280mm,<br>340mm | Stainless Steel |
| 24553-492 | 6U | 235mm | 1 | DIN Connector | 160mm,<br>220mm                     | Stainless Steel |
| 24553-493 | 6U | 295mm | 1 | DIN Connector | 160mm,<br>220mm,<br>280mm           | Stainless Steel |
| 24553-494 | 6U | 355mm | 1 | DIN Connector | 160mm,<br>220mm,<br>280mm,<br>340mm | Stainless Steel |

Table 2/3

| Catalog Number | Handle Included | Mounting | Complies With   | Finish               | Material | Rack Width |
|----------------|-----------------|----------|-----------------|----------------------|----------|------------|
| 24553-192      | No              | Rack     | IEC 60297-3-103 | Anodized, Passivated | Aluminum | 84HP       |
| 24553-193      | No              | Rack     | IEC 60297-3-103 | Anodized, Passivated |          | 84HP       |
| 24553-194      | No              | Rack     | IEC 60297-3-103 | Anodized, Passivated |          | 84HP       |
| 24553-492      | No              | Rack     | IEC 60297-3-103 | Anodized, Passivated |          | 84HP       |
| 24553-493      | No              | Rack     | IEC 60297-3-103 | Anodized, Passivated |          | 84HP       |
| 24553-494      | No              | Rack     | IEC 60297-3-103 | Anodized, Passivated |          | 84HP       |

Table 3/3

| Catalog Number | Quick Ship |
|----------------|------------|
| 24553-192      | No         |
| 24553-193      | No         |

| Catalog Number | Quick Ship |
|----------------|------------|
| 24553-194      | No         |
| 24553-492      | No         |
| 24553-493      | No         |
| 24553-494      | No         |

## ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**