

# Interscale Desktop Case, Perforated



Flexible desktop case with integrated EMC protection and perforated sides. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

## CERTIFICATIONS



## FEATURES

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

## SPECIFICATIONS

|                           |                        |
|---------------------------|------------------------|
| <b>Material:</b>          | Aluminum; Steel        |
| <b>Type:</b>              | Desktop                |
| <b>Product Family:</b>    | Interscale             |
| <b>Protection Rating:</b> | IP20                   |
| <b>Color Code:</b>        | RAL 7016               |
| <b>Product Type:</b>      | Small Form Factor Case |

Table 1/2

| Catalog Number | Height  | Package Quantity | Width | Depth | Cooling    | Color           |
|----------------|---------|------------------|-------|-------|------------|-----------------|
| 14825-154      | 43.7mm  | 1                | 221mm | 177mm | Perforated | Anthracite Grey |
| 14825-254      | 88.1mm  | 1                | 221mm | 177mm | Perforated | Anthracite Grey |
| 14825-155      | 43.7mm  | 1                | 221mm | 221mm | Perforated | Anthracite Grey |
| 14825-175      | 43.7mm  | 1                | 310mm | 221mm | Perforated | Anthracite Grey |
| 14825-195      | 43.7mm  | 1                | 399mm | 221mm | Perforated | Anthracite Grey |
| 14825-197      | 43.7mm  | 1                | 399mm | 310mm | Perforated | Anthracite Grey |
| 14825-255      | 88.1mm  | 1                | 221mm | 221mm | Perforated | Anthracite Grey |
| 14825-275      | 88.1mm  | 1                | 310mm | 221mm | Perforated | Anthracite Grey |
| 14825-295      | 88.1mm  | 1                | 399mm | 221mm | Perforated | Anthracite Grey |
| 14825-297      | 88.1mm  | 1                | 399mm | 310mm | Perforated | Anthracite Grey |
| 14825-375      | 132.6mm | 1                | 310mm | 221mm | Perforated | Anthracite Grey |
| 14825-395      | 132.6mm | 1                | 399mm | 221mm | Perforated | Anthracite Grey |
| 14825-397      | 132.6mm | 1                | 399mm | 310mm | Perforated | Anthracite Grey |

Table 2/2

| Catalog Number | Finish                              | Quick Ship |
|----------------|-------------------------------------|------------|
| 14825-154      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-254      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-155      | Aluminum-Zinc Plated, Powder Coated | No         |

| Catalog Number | Finish                              | Quick Ship |
|----------------|-------------------------------------|------------|
| 14825-175      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-195      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-197      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-255      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-275      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-295      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-297      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-375      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-395      | Aluminum-Zinc Plated, Powder Coated | No         |
| 14825-397      | Aluminum-Zinc Plated, Powder Coated | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**