

Varistar Server Cabinet, RAL 9003, Side-by-Side



Server rack for high static load requirements, completely assembled and grounded including side by side kits powder coated in white.

CERTIFICATIONS



FEATURES

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different servers possible

Server cabinet with perforated doors, airflow rate 78 %

RAL 9003 (white)

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Frame Material	Cladding Material	Frame Color	Frame Color Code	Cladding Color
12130-275	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-276	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-285	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White

CatalogNumber	Type	Frame Material	Cladding Material	Frame Color	Frame Color Code	Cladding Color
12130-286	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-279	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-280	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-289	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-290	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-283	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-284	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-293	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White
12130-294	Side-by-Side	Steel	Steel	Signal White	RAL 9003	Signal White

Table 2/3

Catalog Number	Cladding Color Code	Rack Height	Height	Width	Depth	Static Load
12130-275	RAL 9003	42U	2000mm	600mm	1000mm	1600kg
12130-276	RAL 9003	42U	2000mm	800mm	1000mm	1600kg
12130-285	RAL 9003	42U	2000mm	600mm	1200mm	1600kg
12130-286	RAL 9003	42U	2000mm	800mm	1200mm	1600kg
12130-279	RAL 9003	47U	2200mm	600mm	1000mm	1600kg
12130-280	RAL 9003	47U	2200mm	800mm	1000mm	1600kg
12130-289	RAL 9003	47U	2200mm	600mm	1200mm	1600kg

CatalogNumber	Cladding Color Code	Rack Height	Height	Width	Depth	Static Load
12130-290	RAL 9003	47U	2200mm	800mm	1200mm	1600kg
12130-283	RAL 9003	52U	2450mm	600mm	1000mm	1600kg
12130-284	RAL 9003	52U	2450mm	800mm	1000mm	1600kg
12130-293	RAL 9003	52U	2450mm	600mm	1200mm	1600kg
12130-294	RAL 9003	52U	2450mm	800mm	1200mm	1600kg

Table 3/3

Catalog Number	Quick Ship
12130-275	No
12130-276	No
12130-285	No
12130-286	No
12130-279	No
12130-280	No
12130-289	No
12130-290	No
12130-283	No
12130-284	No
12130-293	No
12130-294	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE