

BC200-CD Conduit to Beam Clamp



CERTIFICATIONS







FEATURES

Eliminates offset bending conduit


Threaded hole on back

Ideal for electrical, mechanical, and HVAC applications

SPECIFICATIONS

Table 1/2								
Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	Flange Thickness (FT)	Rod Size (RS)		
BC200CD1B	182220	Steel	Electrogalvaniz ed	19 - 25 mm	16 mm Max	6		

Table 2/2							
Catalog Number	Article Number	Torque (TQ)	Static Load				
BC200CD1B	182220	4 N·m	440N				



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

