

# Branch Line Restraint Structure Attachment to Wood/Concrete

## Data Solutions



### CERTIFICATIONS



### FEATURES

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to wood or concrete where cracked concrete approval is not needed

### SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material | Finish            | Rod Size (RS) | Height (H) | Length (L) |
|----------------|----------------|----------|-------------------|---------------|------------|------------|
| CSBBRS2MEG     | 402240         | Steel    | Electrogalvanized | 10, 12        | 28.2mm     | 40.4mm     |

Table 2/2


| Catalog Number | Article Number | Width (W) | Screw Length (L) | Drill Bit Diameter |
|----------------|----------------|-----------|------------------|--------------------|
|----------------|----------------|-----------|------------------|--------------------|

|            |        |        |        |     |
|------------|--------|--------|--------|-----|
| CSBBRS2MEG | 402240 | 26.9mm | 44.5mm | 5mm |
|------------|--------|--------|--------|-----|

### ADDITIONAL PRODUCT DETAILS

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE