


# Partial SF Transversal Support Bar, SFBP



These support bars enable partial height swing frames to be mounted in wall mounted and floor standing steel enclosures, providing a strong fixation method.

## FEATURES

Description: Enables partial height swing frames to be mounted in wall mounted, steel enclosures, and floor standing, combinable, steel enclosures. The swing frames can be mounted to allow both left and right hand opening.

Material: 3 mm zinc plated steel.

Pack quantity: 1 complete kit including mounting brackets for one swing frame.

Mounting requirements: For wall mounted, steel enclosures, use in combination with the AVB profiles. For floor standing enclosures, it can be mounted directly to the enclosure frame or adjustable in depth, in steps of 25 mm, by means of the CLPK.

SPECIFICATIONS

**Thickness:** 3mm  
**Material:** Mild Steel  
**Finish:** Zinc Plated

| Table 1/1      |                |        |       |       |                    |            |
|----------------|----------------|--------|-------|-------|--------------------|------------|
| Catalog Number | Article Number | Height | Width | Depth | Enclosure Material | Quick Ship |
| SFBP600        | SFBP600        | 106mm  | 600mm | 31mm  | Mild Steel         | No         |
| SFBP800        | SFBP800        | 106mm  | 800mm | 31mm  | Mild Steel         | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE